

# Steripur 317

## Pneumatically Operated Valve DN 8 - 20 mm (3/8" - 3/4")



#### **Features**

- High cycle stainless steel piston actuator
- Compact design, the outside diameter of the actuator is the same size as the bonnet flange
- Advantages in multiport bodies and manifold valve assemblies
- Control air connection in flow direction
- CDSA sealing concept, see page 32
- Flexible diaphragm suspension
- Encapsulated diaphragm
- Clean and polished exterior design ideal for sterile wash downs

### **Optional**

- Available with a wide range of control equipment and accessories see page 132 to 139, also for retrofitting
- Control air connection 90° to flow direction
- Autoclavable

#### **Technical Data**

Control function (Cf.): Pneumatically operated

Fail safe close (NC): Cf. 1 & 4
Fail safe open (NO): Cf. 2 & 5
Double acting (DA): Cf. 3 & 6
At control function NO/DA higher control pressure than required may affect the lifetime of the working diaphragm.

Direction

Control connection: At Cf. 4, 5 & 6 in flow direction, standard

At Cf. 1, 2 & 3, 90° to flow direction

Max. working pressure: Unidirectional (delta p = 100%)

EPDM diaphragm 8 bar (115 psi) PTFE diaphragm 7 bar (100 psi)

Higher working pressure may be achieved with different actuator. Please consult a SED factory representative for working pressure above the indicated maximum.

Max. working temperature: 160°C (320°F) dependent on application

Control pressure: Cf. 1 & 4 4,2 - 7 bar (60 - 100 psi) Cf. 2, 3, 5 & 6 4 - 5 bar (60 - 72 psi)

Diaphragm material: EPDM or PTFE

Valve body material: Forged 1.4435/ 316 L ASME/BPE

Investment cast 1.4435/316 L

Other alloys

End connection: Butt weld ends see fold out page 21

Clamps and flanges see page 22 to 24

Special ends

Actuators suitable for: Two-Way bodies

Welded configurations

T-bodies


Multiport bodies
Tank bottom bodies

Flow rate: Kv in m<sup>3</sup>/h (Cv in GPM) see page 9

Diaphragm size: MA 10 Weight: ca. 1,0 kg

Technical data also valid for multiport valve.

DN		Filling volume (NL)	
(mm)	MA	NC	NO/DA
8-20	25	0,035	0,030



Red indicated values for DA Version

Valve type overview see page 26 and 27.

Ordering key see page 66 to 68.